SPECIFICATIONS



WF168WA05/06 6½" glass fibre cone mid/woofers, 4/8 ohm

WF168WA05/06 are mid/woofers designed for demanding bass and midrange applications. They work equally well for high-end hi-fi, high quality home theater systems, and top multimedia setups, etc.

Powered by a large 90 mm magnet structure that ensures good efficiency and optimal T/S parameters.

The large 32 mm voice coil ensures high power handling - thermally and mechanically

The new optimized woven glass fibre cone ensures large bandwidth and low distortion. Distortion is further reduced by efficient venting and by adding an internal alu shorting ring to stabilize the magnetic field in the air gap.

FFATURES

- · New optimized glass fibre cone design
- Rigid steel chassis with extensive venting for lower air flow speed reducing audible distortion
- · Vented center pole with dual flares for reduced noise level at large cone excursions
- Heavy-duty fiber glass voice coil former to reduce mechanical losses resulting in better dynamic performance and low-level details
- · Large motor structure for better control and power handling
- Built-in alu field-stabilizing ring for reduced distortion at high levels
- Low-loss suspension (high Qm) for better reproduction of details and dynamics
- · Black plated motor parts for better heat transfer to the surrounding air
- Conex spider for better durability under extreme conditions
- · Gold plated terminals to ensure long-term trouble free connection
- Delivered with foam gasket attached for hassle-free mounting and secure cabinet sealing



NOMINAL SPECIFICATIONS

| | Parameter | WF168WA05 | | WF168WA06 | | |
|-------|--|-------------------|------------------|-------------------|------------------|---------|
| Notes | | Before burn-in | After burn-in | Before burn-in | After burn-in | Unit |
| | Nominal size | | 1/2 | | 1/2 | [inch.] |
| | Nominal impedance | 4 | | 8 | | [ohm] |
| | Recommended max. upper frequency limit | 3 | | 3 | | [kHz] |
| 1, 3 | Sensitivity, 2.83V/1m (average 400-3,000 Hz) | 91 | | 88 | | [dB] |
| 2 | Power handling, short term, IEC 268-5, no additional filtering | | | | | [W] |
| 2 | Power handling, long term, IEC 268-5, no additional filtering | | | | | [W] |
| 2 | Power handling, continuous, IEC 268-5, no additional filtering | 60 | | 60 | | [W] |
| | Effective radiating area, S _d | 131 | | 131 | | [cm²] |
| 3, 6 | Resonance frequency (free air, no baffle), Fs | 40 | | 41 | | [Hz] |
| | Moving mass, incl. air (free air, no baffle), Mms | 14 | 14.0 | | 13.4 | |
| 3 | Force factor, Bxl | 5.0 | | 6.4 | | [N/A] |
| 3, 6 | Suspension compliance, C _{ms} | 1.14 | | 1.14 | | [mm/N] |
| 3, 6 | Equivalent air volume, Vas | 27.7 | | 27.7 | | [lit.] |
| 3, 6 | Mechanical resistance, Rms | 0.49 | | 0.49 | | [Ns/m] |
| 3, 6 | Mechanical Q, Qms | 7.2 | | 7.0 | | [-] |
| 3, 6 | Electrical Q, Qes | 0.45 | | 0.54 | | [-] |
| 3, 6 | Total Q, Qts | 0.42 | | 0.50 | | [-] |
| 4 | Voice coil resistance, RDC | 3.2 | | 6.4 | | [ohm] |
| 5 | Voice coil inductance, Le (measured at 10 kHz) | 0.24 | | 0.40 | | [mH] |
| | Voice coil inside diameter | 32 | | 32 | | [mm] |
| | Voice coil winding height | 11 | | 11 | | [mm] |
| | Air gap height | 5 | | 5 | | [mm] |
| | Theoretical linear motor stroke, Xmax | ±3 | | ±3 | | [mm] |
| | Magnet weight | 4 | 00 | 40 | 00 | [g] |
| | Total unit net weight excl. packaging | 1. | 06 | 1. | 06 | [kg] |
| 3, 5 | K _{rm} | 0.11 | | 0.085 | | [mohm] |
| 3, 5 | E _{rm} | 1.01 | | 1.07 | | [-] |
| 3, 5 | K _{xm} | 4 | .1 | 6 | .7 | [mH] |
| 3, 5 | E _{xm} | 0. | 71 | 0. | 71 | [-] |


- Note 1 Measured in infinite baffle.
- Note 2 Tested in free air (no cabinet).
- Note 3 Measured using a semi-constant current source, nominal level 2 mA.
- Note 4 Measured at 25 deg. C
- Note 5 It is generally a rough simplification to assume that loudspeaker transducer voice coils exhibit the characteristics of an inductor. Instead it is a far more accurate approach to use the more advanced model often referred to as the "Wright empirical model", also used in LEAP-4 as the TSL model (www.linearx.com), involving parameters K_{TTM}, E_{TTM}, K_{XTM}, and E_{XTM}. This more accurate transducer model is described in a technical paper here at our web site.
- Note 6 After burn-in specifications are measured 12 hours after exiting the transducer by a 20 Hz sine wave for 2 hours at level 10/14.1 V_{RMS} (4/8 ohm version). The unit is not burned in before shipping.

Specifications are subject to change without any further notice. Copyright © 2014 by Wavecor Ltd., Guangzhou, China. All rights reserved. Wavecor® is a registered trademark of Wavecor Ltd. For more information please visit www.Wavecor.com


SPECIFICATIONS




WF168WA05/06 6½" glass fibre cone mid/woofers, 4/8 ohm




Measuring conditions, SPL
Driver mounting: Flush in infinite
baffle, back side open (no cabinet)
Microphone distance: 1.0 m
Input signal: 2.83 VRMS stepped sine
wave
Smoothing: 1/6 oct.



Measuring conditions, impedance Driver mounting: Free air, no baffle, back side open (no cabinet) Input signal: Stepped sine wave, semicurrent-drive, nominal current 2 mA Smoothing: None



Measuring conditions, SPL
Driver mounting: Flush in infinite
baffle, back side open (no cabinet)
Microphone distance: 1.0 m
Input signal: 2.83 VRMS stepped sine
wave
Smoothing: 1/6 oct.



Measuring conditions, impedance Driver mounting: Free air, no baffle, back side open (no cabinet) Input signal: Stepped sine wave, semicurrent-drive, nominal current 2 mA Smoothing: None

Specifications are subject to change without any further notice. Copyright © 2014 by Wavecor Ltd., Guangzhou, China. All rights reserved. Wavecor® is a registered trademark of Wavecor Ltd.


For more information please visit www.Wavecor.com




WF168WA05/06 6½" glass fibre cone mid/woofers, 4/8 ohm

OUTLINE DRAWING (nominal dimensions)


Dimensions in mm





May 5, 2014

CONNECTIONS



Thickness, both terminals: 0.5 mm Terminal plating: Gold

PACKAGING AND ORDERING INFORMATION

| Part no. WF168WA05-01 | 4 ohm version, individual packaging (one piece per box) |
|-----------------------|---|
| Part no. WF168WA05-02 | 4 ohm version, bulk packaging |
| Part no. WF168WA06-01 | 8 ohm version, individual packaging (one piece per box) |
| Part no. WF168WA06-02 | 8 ohm version, bulk packaging |

Latest update: October 14, 2014